

I.W. Tremont Co., Inc.

Filter & Technical Specialty Papers

79 Fourth Avenue - Hawthorne, New Jersey 07506

Tel: 973-427-3800

Fax: 973-427-3778

www.iwtremont.com

Technical Data Sheet

Material Designation

LL-84

Material Properties
Summary

Binderless Organic Binder Double Laminated
 Acrylic Binder Laminated Hydrophobic

This laminated glass product is a high efficiency, hydrophobic, multi-purpose filter medium with good heat resistance. It is particularly recommended for both gas and liquid filtration in the medical field and for monitoring applications.

The base material consists of glass microfibers with 3-7% acrylic resin binder. The supporting scrim is a 0.5 oz/yd² Reemay, a high strength spun bonded polyester nonwoven. The scrims are applied to both sides.

The scrims are bonded to the glass media using a polyester hot melt which has a melting point of 325 degrees F.

Micron rating

1-2

μm

Basis Weight

75

lbs/3,000 ft²
TAPPI Method T410

Caliper Thickness

0.017

inches - 4 psi
TAPPI Method T411

Mean Pore Size

3.1

μm

DOP Smoke Penetration

0.015

% at 0.3 μm @
10.5 ft/minute

ASTM Method D-2986

Air Flow Resistance

40

mm H₂O @
10.5 ft/minute

ASTM Method D-2986

Tensile Strength MD

4.5

lbs / inches
TAPPI Method T494

Tensile Strength CD

-

lbs / inches
TAPPI Method T494

Dry Elongation MD

-

%

TAPPI Method T494

Dry Elongation CD

-

%

TAPPI Method T494

Frazier Permeability

-

ft³ / min / ft² @
0.5in H₂O W.G.

ASTM Method F778-82

Gurley Stiffness

-

mg

TAPPI Method T543

Water Repellency

20.0

Inches H₂O

Ignition Loss

-

% Loss

Comments:

Actual filtration performance, i.e. efficiency and dust holding capacity, will vary depending upon filter design parameters and the normal variation of the media properties consistent with the specification range. We continuously strive to define our products and hence the specifications are subject to change.